



# LI-FCB-4T1-SS-2M-NP-T1



**Address:**

48820 Kato Road  
Suite 100B  
Fremont, CA 94538  
USA



**Phone:**

+1 (408)263-0988

**Fax:**

+1 (408)217-1960



**Sales:**

[sales@leopardimaging.com](mailto:sales@leopardimaging.com)

**Support:**

[support@leopardimaging.com](mailto:support@leopardimaging.com)

## FEATURES

- Supports E3653-A03 board
- Compatible with Nvidia Jetson platform
- Length: 2 m
- Weight: ~ 170 g
- Part#: LI-FCB-4T1-SS-2M-NP-T1



AUTO FAKRA  
QTY: 4  
IP Rating: IP67




MATE - AX TO AUTO FAKRA



MATE – AX  
QTY: 1  
Waterproof: No

## MECHANICAL DIAGRAM



### Assembly components:

Item NO	Part#	Description	QTY	U/M
1	2381749 - 1	Coax cable, AWG 30, DACAR 302 - 3	2036	MM
2	2298126 - 1	MATE - AX, Crimp Ferrule, RTK031	4	PC
3	2298121 - 1	MATE - AX, Socket Center Contact, RTK031	4	PC
4	2298116 - 1	4POS, MATE – AX, SOC HSG ASSY, 180DEG, COD Z	4	PC
5	2298721 - 2	Plug Housing, MATE - AX, 4P, Female, Unsealed, Key B	1	PC
6	2272633 - 3	Outer Ferrule, FAKRA AUTO, Sealed, RTK031	4	PC
7	2203270 - 8	Socket Center Contact, FAKRA AUTO, RTK031	4	PC
8	2203274 - 3	Socket Cavity Subassy, FAKRA AUTO, RTK031	4	PC
9	2307194 - 2	Inner Housing, Female, FAKRA AUTO, Sealed	4	PC
10	2 – 2307383 - 0	Outer Housing, Female, FAKRA AUTO, Sealed, Code Z, Black	4	PC
11	963245 - 1	Wire Seal, FAKRA AUTO, RTK031	4	PC
12	2289592 - 3	Seal Cover, FAKRA AUTO, RTK031	4	PC
13	291172 - 3	Label TAG3TD3 - 1209 - WHCL	1	EA

### NOTE:

1 Electrical test according to TE specification 108-18857. Standard test 3.1.1

Cutting length to be fixed by manufacturing

Manufacturing code applied after successful electrical test

## ● REVISION HISTORY

Revision	Description	Release Date
1.0	First release.	22 June 2022

48820 Kato Rd, Suite 100B, Fremont, CA 94538, USA  
Phone: +1 (408)263-0988  
Fax: +1(408)217-1960  
Email: [sales@leopardimaging.com](mailto:sales@leopardimaging.com)  
Website: [www.leopardimaging.com](http://www.leopardimaging.com)

