




LEOPARD
IMAGING

LI-USB30-IMX274



Address:

910 Auburn Ct
Fremont, CA 94538
USA



Phone:

+1 (408)263-0988

Fax:

+1 (408)217-1960



Sales:

sales@leopardimaging.com

Support:

support@leopardimaging.com

KEY FEATURES

- USB 3.0 Super Speed support
- RAW data output without compression
- UVC compliant
- Color camera
- Supports M12 (Default) / CS lens
- Allows customization
- USB + 5 VDC powered device
- Part#: LI-USB30-IMX274

DEFAULT LENS SPECIFICATION

Effective Focal Length	3.25 mm \pm 5%
Aperture, F/#	2.60 \pm 5%
Field of View (FOV)	87.9° horizontal
	56.2° vertical
TV Distortion	< -0.55%
IR Filter	650 nm IR cut filter
Lens Mount	M12 x P0.5

APPLICATIONS


- Machine Vision
- Medical Camera
- Scientific Camera

SDK SUPPORTED

- Camera Tool Source Code in C#
- Capture & Display
- RAW to RGB Conversion
- Save file as BMP & RAW format
- Color Matrix

BOM

#	Items	QTY
1	LI-IMX274-MIPI-M12	1
3	LI-USB30 main board	1
4	MIPI adapter board	1
5	FAW-1233-02 (200 mm)	1



RAW data streaming



Camera Tool view mode

SPECIFICATIONS

Optical Specification	
Sensor	Sony Diagonal 7.20 mm (Type 1/2.5) CMOS Image Sensor IMX274
Optical Format	1/2.5"
Resolution	3864 (H) x 2196 (V) (active pixels)
Pixel Size	1.62 x 1.62 μm
Frame Rate	30 fps @ 1920 x 1080
Shutter	Rolling
IR Filter (on Lens)	650 nm IR cut filter
Color / Mono	Color sensor
Operating Temp	-20°C ~ +75°C
Storage Temp	-20°C ~ +75°C
Lens Mount	M12 / CS (Default: M12)
Register Access Function	Supported
Electrical Specification	
Interface	USB 3.0
Power Supply	USB 3.0 + 5 VDC power source
Power Consumption	183 mA @ 5 VDC
Mechanical Specification	
Dimensions	LI-IMX274-MIPI: 38.0 (L) x 38.0 (W) mm
	USB 3.0 MIPI Tester: 56.0 (L) x 26.0 (W) mm
Weight	~ 32 g

● REVISION HISTORY

Revision	Description	Release Date
1.0	First release.	25 Dec 2020
1.1	Updated lens information.	03 Mar 2022
1.2	Updated product pic.	04 Apr 2023

910 Auburn Ct, Fremont, CA 94538, USA

Phone: +1-408-263-0988

Fax: +1-408-217-1960

Email: sales@leopardimaging.com

Website: www.leopardimaging.com

