LI-XAVIER-KIT-IMX377CS-X Data Sheet

Key Features

- Compatible with Nvidia® Jetson AGX Xavier™ Developer Kit
- MIPI CSI-2 interface
- Supports up to four 4-lane cameras
- Sony Diagonal 7.81 mm (Type 1/2.3) CMOS Image Sensor IMX377CQT
- Active pixels: 4024 (H) x 3036 (V)
- Pixel size: 1.55 x 1.55 µm
- Color camera
- Length of the I-PEX cable: 300 mm
- Supports multiple length cables
- Connector Part#: 20525-030E-02
- Supports IR cut switch
- Supports CS lens
- Allows customization
- Part#:

(1 cam) LI-XAVIER-KIT-IMX377CS
(2 cam) LI-XAVIER-KIT-IMX377CS-D
(3 cam) LI-XAVIER-KIT-IMX377CS-T
(4 cam) LI-XAVIER-KIT-IMX377CS-Q

Applications

- Industrial Cameras
- Surveillance cameras



Lens Spec

- Focal Length: 5.0 mm
- Aperture, F/#: 2.2
- FOV (D / H / V): 87° / 76° / 43°
- TV Distortion: < -8%
- Mount Type: CS

BOM

Nvidia AGX Xavier Developer Kit not included

#	Items	QTY
1	LI-JXAV-MIPI-ADPT-4CAM	1
2	LI-IMX377-MIPI-CS	1,2,3 or 4
3	FAW-1233-03 cable	1,2,3 or 4

Leopard Imaging Inc.
910 Auburn Ct, Fremont, CA 94538, USA
Phone: +1-408-263-0988
Fax: +1-408-217-1960
Email: sales@leopardimaging.com
Website: www.leopardimaging.com

LI-XAVIER-KIT-IMX377CS

BOM

#	Items	QTY
1	LI-JXAV-MIPI-ADPT-4CAM	1
2	LI-IMX377-MIPI-CS	1
3	FAW-1233-03 cable	1



LI-XAVIER-KIT-IMX377CS-D

BOM

#	Items	QTY
1	LI-JXAV-MIPI-ADPT-4CAM	1
2	LI-IMX377-MIPI-CS	2
3	FAW-1233-03 cable	2

LI-XAVIER-KIT-IMX377CS-T

BOM

#	Items	QTY
1	LI-JXAV-MIPI-ADPT-4CAM	1
2	LI-IMX377-MIPI-CS	3
3	FAW-1233-03 cable	3



LI-XAVIER-KIT-IMX377CS-Q

BOM

#	Items	QTY
1	LI-JXAV-MIPI-ADPT-4CAM	1
2	LI-IMX377-MIPI-CS	4
3	FAW-1233-03 cable	4



Leopard Imaging Inc.

910 Auburn Ct, Fremont, CA 94538, USA
Phone: +1-408-263-0988
Fax: +1-408-217-1960
Email: sales@leopardimaging.com
Website: www.leopardimaging.com

Dimensions

LI-IMX377-MIPI-CS



LI-JXAV-MIPI-ADPT-4CAM



FAW-1233-03



Leopard Imaging Inc.

910 Auburn Ct, Fremont, CA 94538, USA Phone: +1-408-263-0988
Fax: +1-408-217-1960
Email: sales@leopardimaging.com
Website: www.leopardimaging.com

LI-JXAV-MIPI-ADPT-4CAM





Interfaces

Interface J1

- Part#: 20525-030E-02
- Number of Positions: 30
- Pitch: 0.4 mm
- Mating I-PEX cable: FAW-1233-03 (300 mm)



Interface J2

- Part#: 20525-030E-02
- Number of Positions: 30
- Pitch: 0.4 mm
- Mating I-PEX cable: FAW-1233-03 (300 mm)



Interface J3

- Part#: 20525-030E-02
- Number of Positions: 30
- Pitch: 0.4 mm
- Mating I-PEX cable: FAW-1233-03 (300 mm)



Leopard Imaging Inc.

910 Auburn Ct, Fremont, CA 94538, USA
Phone: +1-408-263-0988
Fax: +1-408-217-1960
Email: sales@leopardimaging.com
Website: www.leopardimaging.com

Interface J4

- Part#: 20525-030E-02
- Number of Positions: 30
- Pitch: 0.4 mm
- Mating I-PEX cable: FAW-1233-03 (300 mm)



Interface J5

- Part#: 0894000220
- Number of Positions: 2
- Pitch: 2 mm



Interface J10

- Part#: QTH-060-01-L-D-A
- Number of Positions: 120
- Number of Rows: 2
- Pitch: 0.5 mm



Leopard Imaging Inc.

910 Auburn Ct, Fremont, CA 94538, USA
Phone: +1-408-263-0988
Fax: +1-408-217-1960
Email: sales@leopardimaging.com
Website: www.leopardimaging.com

LI-IMX377-MIPI-CS

Camera Spec	
Image sensor	Sony Diagonal 7.81 mm (Type 1/2.3) CMOS Image Sensor IMX377CQT
Optical format	1/2.3"
Number of active pixels	4024 (H) x 3036 (V)
Pixel size	1.55 x 1.55 µm
Color or Mono	Color
Interface	MIPI interface
Lens mount	CS
IR switcher	Support
Weight	~ 56 g
Interfaces	
Interface J1: ▪ Part#: 20525-030E-02C ▪ Number of Positions: 30 ▪ Pitch: 0.4 mm ▪ Mating I-PEX cable: FAW-1233-03 (300 mm)	
Interface J3: ▪ Part#: 1734829-2 ▪ Number of Positions: 2 ▪ Pitch: 1.25 mm	

Leopard Imaging Inc.

910 Auburn Ct, Fremont, CA 94538, USA
Phone: +1-408-263-0988
Fax: +1-408-217-1960
Email: sales@leopardimaging.com
Website: www.leopardimaging.com

Revision History

Revision	Description	Release Date
1.0	First release.	11. May. 2019
1.1	Deleted info quoted from sensor spec.	26. May. 2022
1.2	Deleted lens model info.	04. Aug. 2023

910 Auburn Ct, Fremont, CA 94538, USA
Phone: +1-408-263-0988
Fax: +1-408-217-1960
Email: sales@leopardimaging.com
Website: www.leopardimaging.com