


LI-RAA462113-MIPI-CS

Data Sheet

Key Features


- Renesas 8MP CMOS Image Sensor RAA462113
- Optical format: 1/1.9"
- Effective pixels: 3872 (H) x 2192 (V)
- Pixel size: 1.85 x 1.85 μm
- Color sensor
- Interface: MIPI output
- FPGA included
- High sensitivity
- Low noise
- Supports CS lens (Lens not included)
- 650 nm IR cut filter included
- Connector: 20525-030E-02
- Mating cable: FAW-1233-xx
- Supports multiple length cables
- Module size: 38 x 38 mm
- Weight (without lens): ~ 20 g
- Part#: **LI-RAA462113-MIPI-CS**



Interfaces


Interface J4:

- Part#: 20525-030E-02
- Number of Positions: 30
- Pitch: 0.4 mm
- Mating I-PEX cable: LI-FAW-1233-xx




Interface J8:

- Part#: 1734829-2
- Number of Positions: 2
- Pitch: 1.25 mm




Interface J6:

- Part#: 1734829-2
- Number of Positions: 2
- Pitch: 1.25 mm




Interface J2:

- Part#: 20021321-00010C4LF
- Number of Positions: 10
- Pitch: 1.27 mm



Interface J3:

- Part#: 20021321-00006C4LF
- Number of Positions: 6
- Pitch: 1.27 mm



Leopard Imaging Inc.

910 Auburn Ct, Fremont, CA 94538, USA
 Phone: +1-408-263-0988
 Fax: +1-408-217-1960
 Email: sales@leopardimaging.com
 Website: www.leopardimaging.com

Revision History

Revision	Description	Release Date
1.0	First release.	31. Mar. 2019
1.1	Deleted info quoted from sensor spec.	27. May. 2022



Leopard Imaging Inc.

910 Auburn Ct, Fremont, CA 94538, USA
Phone: +1-408-263-0988
Fax: +1-408-217-1960
Email: sales@leopardimaging.com
Website: www.leopardimaging.com