



LEOPARD
IMAGING


Rev 1.2

LI-JETSON-KIT-IMX377CS-X

Data Sheet

Key Features

- Compatible with Nvidia Jetson TX1/TX2 Development Kit
- MIPI CSI-2 interface
- Supports up to three cameras
- Adapter board:
LI-JTX1-MIPI-ADPT
Includes three 4-lane interfaces
Support 13M @ 30 fps
- Sony Diagonal 7.81 mm (Type 1/2.3)
CMOS Image Sensor IMX377CQT
- Active pixels: 4024 (H) x 3036 (V)
- Pixel size: 1.55 x 1.55 μm
- Color camera
- I-PEX cable part#: FAW-1233-03
- Length of the I-PEX cable: 300 mm
- Supports multiple length cables
- Connector Part#: 20525-030E-02
- Supports IR cut switch
- Supports CS lens
- Allows customization
- Part#:
(1 cam) **LI-JETSON-KIT-IMX377CS**
(2 cam) **LI-JETSON-KIT-IMX377CS-D**
(3 cam) **LI-JETSON-KIT-IMX377CS-T**



Lens Spec

- Focal Length: 5.0 mm
- Aperture, F/#: 2.2
- FOV (D / H / V): 87° / 76° / 43°
- TV Distortion: < -8%
- Mount Type: CS

BOM

Nvidia TX1/TX2 Development Kit not included

#	Items	QTY
1	LI-JTX1-MIPI-ADPT	1
2	LI-IMX377-MIPI-CS	1,2 or 3
3	FAW-1233-03 cable	1,2 or 3



Leopard Imaging Inc.

910 Auburn Ct, Fremont, CA 94538, USA
Phone: +1-408-263-0988
Fax: +1-408-217-1960
Email: sales@leopardimaging.com
Website: www.leopardimaging.com

LI-JETSON-KIT-IMX377CS

BOM

#	Items	QTY
1	LI-JTX1-MIPI-ADPT	1
2	LI-IMX377-MIPI-CS	1
3	FAW-1233-03 cable	1



LI-JETSON-KIT-IMX377CS-D

BOM

#	Items	QTY
1	LI-JTX1-MIPI-ADPT	1
2	LI-IMX377-MIPI-CS	2
3	FAW-1233-03 cable	2



LI-JETSON-KIT-IMX377CS-T

BOM

#	Items	QTY
1	LI-JTX1-MIPI-ADPT	1
2	LI-IMX377-MIPI-CS	3
3	FAW-1233-03 cable	3




Leopard Imaging Inc.


910 Auburn Ct, Fremont, CA 94538, USA
Phone: +1-408-263-0988
Fax: +1-408-217-1960
Email: sales@leopardimaging.com
Website: www.leopardimaging.com

Dimensions


LI-IMX377-MIPI-CS



LI-JTX1-MIPI-ADPT



FAW-1233-03



Leopard Imaging Inc.

910 Auburn Ct, Fremont, CA 94538, USA



Phone: +1-408-263-0988

Fax: +1-408-217-1960

Email: sales@leopardimaging.com

Website: www.leopardimaging.com


LI-JTX1-MIPI-ADPT



Interfaces


Interface J1

- Part#: 20525-030E-02
- Number of Positions: 30
- Pitch: 0.4 mm
- Mating I-PEX cable: FAW-1233-03 (300 mm)




Interface J2

- Part#: 20525-030E-02
- Number of Positions: 30
- Pitch: 0.4 mm
- Mating I-PEX cable: FAW-1233-03 (300 mm)



Interface J3

- Part#: 20525-030E-02
- Number of Positions: 30
- Pitch: 0.4 mm
- Mating I-PEX cable: FAW-1233-03 (300 mm)




Leopard Imaging Inc.

910 Auburn Ct, Fremont, CA 94538, USA
 Phone: +1-408-263-0988
 Fax: +1-408-217-1960
 Email: sales@leopardimaging.com
 Website: www.leopardimaging.com

Interface J10

- Part#: QTH-060-01-L-D-A
- Number of Positions: 120
- Number of Rows: 2
- Pitch: 0.5 mm



Leopard Imaging Inc.

910 Auburn Ct, Fremont, CA 94538, USA
Phone: +1-408-263-0988
Fax: +1-408-217-1960
Email: sales@leopardimaging.com
Website: www.leopardimaging.com

LI-IMX377-MIPI-CS



Camera Spec	
Image sensor	Sony Diagonal 7.81 mm (Type 1/2.3) CMOS Image Sensor IMX377CQT
Optical format	1/2.3"
Number of active pixels	4024 (H) x 3036 (V)
Pixel size	1.55 x 1.55 μm
Color or Mono	Color
Interface	MIPI interface
Lens mount	CS
IR switcher	Support
Weight	~ 56 g
Interfaces	
Interface J1: - Part#: 20525-030E-02 - Number of Positions: 30 - Pitch: 0.4 mm - Mating I-PEX cable: FAW-1233-03 (300 mm)	
Interface J3: - Part#: 1734829-2 - Number of Positions: 2 - Pitch: 1.25 mm	



Leopard Imaging Inc.

910 Auburn Ct, Fremont, CA 94538, USA
 Phone: +1-408-263-0988
 Fax: +1-408-217-1960
 Email: sales@leopardimaging.com
 Website: www.leopardimaging.com

Revision History

Revision	Description	Release Date
1.0	First release.	19. Apr. 2018
1.1	Deleted info quoted from sensor spec.	24. May. 2022
1.2	Deleted lens model info.	03. Aug. 2023



Leopard Imaging Inc.

910 Auburn Ct, Fremont, CA 94538, USA
Phone: +1-408-263-0988
Fax: +1-408-217-1960
Email: sales@leopardimaging.com
Website: www.leopardimaging.com