



LEOPARD
IMAGING

LI-USB30-IMX454-MIPI-092H



Address:

910 Auburn Ct
Fremont, CA 94538
USA



Phone:

+1 (408)263-0988

Fax:

+1 (408)217-1960



Sales:

sales@leopardimaging.com

Support:

support@leopardimaging.com

Key Features

- USB 3.0 Super Speed support
- UVC compliant
- Multispectral imaging camera
- Supports up to 41 channels
- Default M12 lens
- Allows customization
- USB + 5 VDC powered device
- Part#: **LI-USB30-IMX454-MIPI-092H**

Lens Specifications

Focal Length	3.6 mm
Aperture, F/#	2.1
Field of View (FOV)	92° horizontal
OP Distortion	<-37%
Relative Illumination	>50%
Optical low pass filter	350nm-1150nm, T>90%
Lens Mount	M12 x P0.5



Applications

- Agriculture
- Food inspection
- Industrial
- Spectral Analysis

SDK Supported






- Demo Software & SDK
- Capture & Display
- By combining multispectral image sensor with proprietary, specially designed signal processing software, image data of 41 wavelengths (from 450 nm to 850 nm, in 10 nm intervals) obtained from 8 types of filters can be captured.
- Save file as PGM, ENVI, csv format



SEPCIFICATIONS

General Behavior	
Video Resolution @ Frame Rate	1948 x 1097 @ 30fps
Interface (Optical)	
IR Cut Filter (on holder)	Included
Sensor	Sony Diagonal 6.46 mm (Type 1/2.8) CMOS Image Sensor IMX454
Format	1/2.8"
Color / Mono	Color
Active Pixels	1937 (H) x 1097 (V)
Pixel Size	2.9 x 2.9 μm
Lens Mount	M12
Interface (Electrical)	
Interface	USB 3.0
Supply Voltage	USB 3.0 +5 VDC power source
Power Consumption	247mA @ 5 VDC (1948 x 1097 @ 30 fps)
Weight	
LI-USB30-IMX454-MIPI-092H	~ 85 g
Temp Info (LI-USB30-IMX454-MIPI-092H)	
Operating Temp	-20 °C ~ +70°C
Storage Temp	-30 °C ~ +85 °C
Supported OS	
Windows OS, Standard Linux OS and other OS with full UVC drivers	

DIMENSIONS




NOTE:

- ⊗ marked are important sizes.
- Tolerances for the unmarked refer to the Tolerance table.
- All materials are compliant with RoHS requirements.
- Unit: mm

TOLERANCE TABLE					
LENGTH TOLERANCE		CHAMFER TOLERANCE		ANGLE TOLERANCE	
Size X	Tolerance	Size X	Tolerance	Size X	Tolerance
$0.5 < X \leq 3$	± 0.1	$0.5 < X \leq 3$	± 0.2	$X \leq 10$	$\pm 1^\circ$
$3 < X \leq 6$	± 0.1	$3 < X \leq 6$	± 0.5	$10 < X \leq 50$	$\pm 30'$
$6 < X \leq 30$	± 0.2	$6 < X \leq 30$	± 1	$50 < X \leq 120$	$\pm 20'$
$30 < X \leq 120$	± 0.3	$X > 30$	± 2	$120 < X \leq 400$	$\pm 10'$
$120 < X \leq 400$	± 0.5			$X > 400$	$\pm 5'$
$400 < X \leq 1000$	± 0.8				
$X > 1000$	± 1.2				

INTERFACE OF J3

- Part#: PZ3161212PDGFCNN070
- Number of Positions: 12
- Pitch: 1.27mm



PINOUT DETAILS

Pin No	Pin Name	Description	Pin Type	Voltage Level
1	OPT_IN	Isolated Input of optoisolator	Input	Max 30V
2	NC	No connection	-	-
3	UART_TX	Transmitting end of UART of CYUSB3014	Output	3.3V
4	UART_RX	Receiving end of UART of CYUSB3014	Input	3.3V
5	GND	Field Ground of optoisolator	-	-
6	GND	Digital Ground	-	-
7	5V0	5V power	Power	5V
8	3V3	3.3V power	Power	3.3V
9	GPIO25	General-purpose input/output	Bidir	3.3V
10	GPIO60	General-purpose input/output	Bidir	3.3V
11	GPIO26	General-purpose input/output	Bidir	3.3V
12	GPIO27	General-purpose input/output	Bidir	3.3V

- REVISION HISTORY

Revision	Description	Release Date
1.0	First Release.	12 Aug 2025
1.1	Updated SDK supported.	03 Dec 2025
1.2	Updated SDK supported.	29 Jan 2026

910 Auburn Ct, Fremont, CA 94538, USA
Phone: +1-408-263-0988
Fax: +1-408-217-1960
Email: sales@leopardimaging.com
Website: www.leopardimaging.com

