




LEOPARD
IMAGING

LI-IMX728-GM2B-xxxH-xx-AA



Address:

910 Auburn Ct
Fremont, CA 94538
USA



Phone:

+1 (408)263-0988

Fax:

+1 (408)217-1960



Sales:

sales@leopardimaging.com

Support:

support@leopardimaging.com

INTRODUCTION

The LI-IMX728-GM2B-xxxH-xx-AA is equipped with Sony diagonal 9.30 mm 8.39MP CMOS RGGGB sensor IMX728 and ADI GMSL2 serializer MAX96717G. This camera outputs 3857 x 2177 RAW data.

SPECIFICATIONS



Maximum Frame Rate	30 fps @ 3840 × 2160
Output Format	20-bit / 16-bit / 12-bit / 10-bit RAW data
Sensor	Diagonal 9.30 mm 8.39MP CMOS RGGGB Sensor IMX728
Optical Format	1/1.72"
Resolution	3857 (H) x 2177 (V) (active pixels)
Pixel Size	2.1 x 2.1 μm
Color / Mono	Color sensor
HDR (High Dynamic Range)	Supported
LFM (LED Flicker Mitigation)	Supported
Lens	FOV H 30° / 70° / 120H
Serializer	ADI MAX96717G
Power Supply Range	9 ~ 19 VDC
Connector	FAKRA Z TYPE
IP Rating	030H: IP69K 070H: TBD 120H: TBD
Power Consumption	Approx. 122 mA @ 12 VDC (3840 x 2160 @ 19 fps)
Operating Temp	-40°C ~ +85°C
Storage Temp	-40°C ~ +85°C
Weight	TBD
Part#	LI-IMX728-GM2B-030H-SF-AA
	LI-IMX728-GM2B-070H-SS-AA
	LI-IMX728-GM2B-120H-SF-AA

APPLICATIONS


- Automotive
 - ◆ High Resolution Front Viewing
 - ◆ Machine Vision
 - ◆ Autonomous Driving
 - ◆ Assisted Driving
 - ◆ Digital Video Recording

CABLE CONNECTOR


- Housing Connector: FAKRA Z Type
- Cable Length: 3 meters



030H




070H



120H


DIMENSIONS: LI-IMX728-GM2B-030H-SF-AA



NOTE:

- $\otimes$ marked are important sizes.
- Other unmarked tolerances are ± 0.3 mm.
- Unit: mm


DIMENSIONS: LI-IMX728-GM2B-070H-SS-AA



NOTE:

- $\otimes$ marked are important sizes.
- Other unmarked tolerances are ± 0.3 mm.
- Unit: mm


DIMENSIONS: LI-IMX728-GM2B-120H-SF-AA



NOTE:

- ⊗ marked are important sizes.
- Other unmarked tolerances are ± 0.3 mm.
- Unit: mm

IMAGE ORIENTATION




ORDERING INFORMATION

NOTE:

xxxH - 030H: FOV H 30° xxxH - 070H: FOV H 70° xxxH - 120H: FOV H 120°

LI-IMX728-GM2B-030H-SF-AA



Lens EFL: $15.34 \pm 2.5\%$ mm


Aperture, F/#: $1.6 \pm 5\%$

Field of View (FOV): 30° (H) / 17° (V) / 34.4° (D)

IR Filter: 650 nm IR cut filter

Mount: Active Alignment (AA)

LI-IMX728-GM2B-070H-SS-AA



Lens EFL: $6.6 \pm 3\%$ mm


Aperture, F/#: $1.6 \pm 5\%$

Field of View (FOV): 70° (H) / 39.3° (V) / 80.1° (D)

IR Filter: 650 nm IR cut filter

Mount: Active Alignment (AA)

LI-IMX728-GM2B-120H-SF-AA



Lens EFL: $4.01 \pm 3\%$ mm


Aperture, F/#: $1.6 \pm 5\%$

Field of View (FOV): 120° (H) / 65° (V) / 140° (D)

IR Filter: 650 nm IR cut filter

Mount: Active Alignment (AA)

SYSTEM BLOCK DIAGRAM



USB3.0 CAMERA KIT

LI-GMSL2-USB



Top View



Bottom View

LI-IMX728-GM2B-xxxH-xx-AA can connect to LI-GMSL2-USB as a USB 3.0 camera.

Part#: **LI-USB30-IMX728-GM2B-xxxH-xx-AA**

SPECIFICATIONS

- USB 3.0 Super Speed support
- UVC compliant
- Allows customization
- 12 VDC Power Supply for camera
- Weight: TBD
- Single Coax Cable transmits up to 12 meters PoC (Power over Cable)
- Resolution: 3840 x 2160 @ 19 fps
- Power consumption: Approx. 122 mA @ 12 VDC
- Compatible with Windows, Linux OS and other OS which have UVC drivers

BOM

#	Items	QTY
1	LI-IMX728-GM2B-xxxH-xx-AA	1
2	LI-GMSL2-USB	1
3	3-Meter Fakra Cable	1
4	12 VDC Power Supply	1
5	USB3.0 Cable	1



SDK SUPPORTED

- Camera Tool Source Code in C#
- Capture & Display
- Register Access Function

● REVISION HISTORY

Revision	Description	Release Date
0.1	Initial draft.	22 May 2025
0.2	Updated Maximum Frame Rate and 030H IP.	29 Sep 2026

910 Auburn Ct, Fremont, CA 94538, USA
Phone: +1-408-263-0988
Fax: +1-408-217-1960
Email: sales@leopardimaging.com
Website: www.leopardimaging.com

